

Tunable emission of RE³⁺ multi-doped glass systems

Daniel dos Santos Francisco¹, Igor Augusto Coetti Magarotto¹, Leonnam Gotardo Merizio¹,
Lucas Carvalho Veloso Rodrigues², Danilo Manzani¹

¹São Carlos Institute of Chemistry (IQSC), University of São Paulo (USP), São Carlos, SP,
Brazil, ²Institute of Chemistry, University of São Paulo

e-mail: daniel.santos.francisco@usp.br

Rare-earth (RE) elements are widely used in electronics, optical fiber amplifiers, laser technologies, and other advanced applications. Despite their extensive use and importance, the purification of rare-earth elements remains expensive due to their similar chemical properties. While the most of works focus on high-pure RE, the expensive purification processes of these elements call attention to reuse and recycling technologies for RE minerals such as monazite and cerite and electronic wastes. Motivated to recycling and study optical applications of varied RE composition materials, we investigate the properties of multi-doped glass samples with general composition RE(100-x)[80Bi(PO₃)₃-10Bi₂O₃-10Na₂O]. The glasses were simultaneously doped with different rare-earth ions (Ce, Pr, Nd, Pm, Sm, Eu, Tb, Dy, Ho, Er, Tm, Yb) at a concentration of 0.2 mol% each, which were added to a total of 2.4%. A non-doped glass sample was also synthesized for comparison. The glass synthesis was performed using the melt-quenching method followed by annealing, resulting in transparent glass samples. Raman spectra suggest that the RE doesn't affect the structure of the glass. It is possible to observe in the UV-Vis spectra several narrow peaks of 4f-4f transitions of the RE³⁺ ions. It was possible to modulate the glass emission according to excitation wavelength used. Excitation at 348 nm resulted in an intense emission bluish emission at around 450 nm from transition ¹D₂→³F₄ of Tm³⁺. When excited at 356 nm, it was observed a white emission mainly due to the bands between 480 and 573 nm mainly from Dy³⁺ emission ⁴F_{9/2}→⁶H_{15/2} and ⁴F_{9/2}→⁶H_{13/2}. [1] Finally, the 393 nm excitation resulted in a reddish emission due to the 611 nm intense band characteristic of Europium ⁵D₀→⁷F₂ transition. [2] These results demonstrate that the glass matrix is able to accommodate different rare-earth ions, resulting in color-tunable emission, opening possibility to optical applications with recycling materials.

Acknowledgements

This work was supported by CNPq grant : 140337/2023-7 and 405048/2021-1.

References

Chen, Yong, et al. "Tunable luminescence mediated by energy transfer in Tm³⁺/Dy³⁺ co-doped phosphate glasses under UV excitation." *Optical Materials* 73 (2017): 535-540.

Binnemans, Koen. "Interpretation of europium (III) spectra." *Coordination Chemistry Reviews* 295 (2015): 1-45.